



SNMG 150612, Grade: CA125P

Order data

Order number	251363 CA125P
GTIN	4960664015634
Item class	25E

Technical description

Main application	P
Cutting conditions	slightly interrupted
Cutting depth a_p	1 - 11 mm
Grade	CA125P
Tool material	Carbide
Corner radius	1.2 mm
Finishing/roughing assignment	Roughing
Cutting speed v_c main application	140 - 330 m/min
ISO code indexable insert	SNMG 150612
Number of changes/inserts	8
Chip breaker	PH
Feed f	0.3 - 1 mm/rev.

Type of product

Indexable insert for turning