


**WNMG 080416, Grade: CA125P****Order data**

Order number	252118 CA125P
GTIN	4960664024490
Item class	25E

Technical description

Corner radius	1.6 mm
Grade	CA125P
Main application	P
Finishing/roughing assignment	Finishing
Cutting conditions	slightly interrupted
Feed f	0.15 - 0.6 mm/rev.
Cutting depth a_p	0.5 - 5 mm
Tool material	Carbide
Chip breaker	PMG
Number of changes/inserts	6
ISO code indexable insert	WNMG 080416
Tolerance	M

Cutting speed v_c main application

150 - 320 m/min

Type of product

Indexable insert for turning