


**CC.T 09T304, Grade: CA125P****Order data**

Order number	260196 CA125P
GTIN	4960664017607
Item class	25E

Technical description

Grade	CA125P
Corner radius	0.4 mm
Cutting speed v_c main application	60 - 260 m/min
Chip breaker	GK
Number of changes/inserts	2
Tool material	Carbide
Finishing/roughing assignment	Finishing
Main application	P
Cutting conditions	slightly interrupted
ISO code indexable insert	CCMT 09T304
Tolerance	M
Feed f	0.1 - 0.3 mm/rev.

Cutting depth a_p	0.5 - 3 mm
Type of product	Indexable insert for turning