

**DC.T 11T304, Grade: CA125P****Order data**

Order number	260386 CA125P
GTIN	4960664018161
Item class	25E

Technical description

Finishing/roughing assignment	Finishing
Corner radius	0.4 mm
Main application	P
Cutting depth a_p	0.5 - 1.5 mm
ISO code indexable insert	DCMT 11T304
Number of changes/inserts	2
Cutting conditions	slightly interrupted
Feed f	0.05 - 0.25 mm/rev.
Cutting speed v_c main application	90 - 260 m/min
Tool material	Carbide
Tolerance	M
Grade	CA125P

Chip breaker	HQ
Type of product	Indexable insert for turning