

**DCMT 070202, Grade: CA125P****Order data**

Order number	260481 CA125P
GTIN	4960664018062
Item class	25E

Technical description

Tool material	Carbide
Corner radius	0.2 mm
Cutting depth a_p	0.5 - 3 mm
Main application	P
Number of changes/inserts	2
Finishing/roughing assignment	Finishing
Cutting conditions	slightly interrupted
ISO code indexable insert	DCMT 070202
Chip breaker	GK
Feed f	0.1 - 0.3 mm/rev.
Cutting speed v_c main application	90 - 260 m/min
Grade	CA125P

Tolerance	M
Type of product	Indexable insert for turning