

**DCMT 070204, Grade: CA125P****Order data**

Order number	260483 CA125P
GTIN	4960664018079
Item class	25E

Technical description

Main application	P
Tool material	Carbide
Cutting depth a_p	0.5 - 3 mm
Tolerance	M
Cutting conditions	slightly interrupted
Corner radius	0.4 mm
Cutting speed v_c main application	90 - 260 m/min
Finishing/roughing assignment	Finishing
Grade	CA125P
ISO code indexable insert	DCMT 070204
Number of changes/inserts	2
Feed f	0.1 - 0.3 mm/rev.

Chip breaker	GK
Type of product	Indexable insert for turning