

**DC.T 11T308, Grade: CA125P****Order data**

Order number	260492 CA125P
GTIN	4960664018116
Item class	25E

Technical description

Finishing/roughing assignment	Finishing
Cutting depth a_p	0.5 - 3 mm
Grade	CA125P
Number of changes/inserts	2
Cutting conditions	slightly interrupted
ISO code indexable insert	DCMT 11T308
Cutting speed v_c main application	90 - 260 m/min
Main application	P
Tolerance	M
Corner radius	0.8 mm
Chip breaker	GK
Tool material	Carbide

Feed f	0.1 - 0.3 mm/rev.
Type of product	Indexable insert for turning