



SNMG 150612, Grade: CA115P

Order data

Order number	251363 CA115P
GTIN	4960664041176
Item class	25E

Technical description

Corner radius	1.2 mm
Cutting speed v_c main application	170 - 380 m/min
Feed f	0.3 - 1 mm/rev.
Main application	P
Finishing/roughing assignment	Roughing
Tool material	Carbide
Number of changes/inserts	8
ISO code indexable insert	SNMG 150612
Cutting conditions	continuous
Chip breaker	PH
Cutting depth a_p	1 - 11 mm
Grade	CA115P

Type of product

Indexable insert for turning