



DNMG 150608, Grade: CA115P

Order data

Order number	250892 CA115P
GTIN	4960664040834
Item class	25E

Technical description

Tool material	Carbide
Cutting depth a_p	1 - 5 mm
Cutting conditions	continuous
Cutting speed v_c main application	170 - 380 m/min
Chip breaker	PH
Main application	P
ISO code indexable insert	DNMG 150608
Finishing/roughing assignment	Roughing
Number of changes/inserts	4
Feed f	0.25 - 0.6 mm/rev.
Grade	CA115P
Corner radius	0.8 mm

Type of product

Indexable insert for turning