


**SNMG 120408, Grade: CA115P****Order data**

Order number	251356 CA115P
GTIN	4960664041145
Item class	25E

Technical description

Main application	P
Tool material	Carbide
Grade	CA115P
Cutting conditions	continuous
ISO code indexable insert	SNMG 120408
Number of changes/inserts	8
Corner radius	0.8 mm
Cutting depth a_p	1 - 11 mm
Chip breaker	PH
Feed f	0.3 - 1 mm/rev.
Finishing/roughing assignment	Roughing
Cutting speed v_c main application	170 - 380 m/min

Type of product

Indexable insert for turning