



Mini LED floodlight, Type: 1000



Order data

| | |
|--------------|---------------|
| Order number | 081451 1000 |
| GTIN | 5708997362006 |
| Item class | 08C |

Description

Version:

Compact and powerful cordless LED floodlights for mobile use. The compact dimensions mean they are perfectly suitable for use as hand lamps. The adjustable magnetic bases allow them to be used as stationary light sources.

New **OPTILight function** for optimised light output and duration. The SMART Grip 4-in-1 system integrates several functions in one unit: a ring for secure grip, a clip for easy attachment, a strong magnet and a base.

Function:

IP65: Protected against jets of water from all directions and protected against penetration by dust (dust-tight), also completely protected against touching.

Supplied with:

Including USB charging cable.

Technical description

| | |
|----------------|------------|
| Overall length | 104 mm |
| Bulb | LED module |
| Weight | 250 g |

Data sheet

| | |
|--|----------------|
| Type of rechargeable battery | Lithium-ion |
| Illumination time | 1.5 - 15 h |
| Overall height | 96 mm |
| Battery voltage | 3.7 V |
| Illumination | 100 - 1000 lm |
| IP Index of Protection | IP 65 |
| Number of rechargeable batteries contained | 1 |
| Power supply | Mains operated |
| Overall width | 38 mm |
| Type of product | Floodlight |