

Garant**Solid carbide milling cutter with chip separators TPC, TiAlN, Ø f8 DC: 5mm****Order data**

Order number	203092 5
GTIN	4067263116929
Item class	11X

Description**Version:**

High-performance end mill for general-purpose applications, **specially designed for TPC applications.**

Strengthened core.

Optimised bending strength due to the use of ultra-fine grain substrates.

Offset chip breakers for controlled chip breaking.

Note:

h_{max} : The values stated in the table are maximum values. For finishing operations we recommend items No. 204012, 204014 and 204015.

$a_{e,max} = 0.07 \times D$ for TPC machining.

Successor product to No. 203089.

Technical description

Cutting edge Ø D_c	5 mm
Shank Ø D_s	6 mm
Number of chip separators	1
Balance quality with shank	G 2.5 with HB
Corner chamfer angle	45 degrees
Recess Ø D_1	4.8 mm
Corner chamfer width at 45°	0.1 mm
Shank	DIN 6535 HB to h6
Overhang length L_1 incl. recess	24 mm

Data sheet

Direction of infeed	horizontal, oblique and vertical
Flute length L_c	17 mm
Tolerance nominal \varnothing	f8
Helix angle	40 degrees
Overall length L	62 mm
No. of teeth Z	5
Average chip thickness h_{max} for TPC milling in Toolox 44 HRC	0.023 mm
Coating	TiAlN
Tool material	Solid carbide
Standard	Manufacturer's standard
Type	N
Helix angle characteristic	unequal spacing
Spacing of the cutters	unequal spacing
Cutting width a_e for milling operation	$0.07 \times D$
Through-coolant	no
Machining strategy	TPC
Colour ring	green
Type of product	End / face mill

User data

	Suitability	V_c	ISO code
Steel < 500 N/mm ²	suitable	380 m/min	P
Steel < 750 N/mm ²	suitable	340 m/min	P
Steel < 900 N/mm ²	suitable	300 m/min	P
Steel < 1100 N/mm ²	suitable	230 m/min	P
Steel < 1400 N/mm ²	suitable	150 m/min	P
TOOLOX 33	suitable	60 m/min	H
TOOLOX 44	suitable	40 m/min	H

Data sheet

HARDOX 500 < 1600 N/mm ²	suitable	25 m/min	H
INOX < 900 N/mm ²	suitable	220 m/min	M
INOX > 900 N/mm ²	suitable only under restricted conditions	150 m/min	M
Uni	suitable		
wet maximum	Suitable		
dry	Suitable only under restricted conditions		
Air	suitable		