

Garant**DC.T 070202, Grade: HB7020****Order data**

Order number	260449 HB7020
GTIN	4045197698896
Item class	21G

Technical description

Main application	P
Feed f	0.1 - 0.3 mm/rev.
Corner radius	0.2 mm
Cutting conditions	slightly interrupted
Cutting speed v_c main application	120 - 350 m/min
Cutting depth a_p	0.5 - 2.5 mm
Chip breaker	SM
Grade	HB7020
Finishing/roughing assignment	Skrubbearbejdning-sletbearbejdning
Tool material	Carbide
ISO code indexable insert	DCMT 070202

Number of changes/inserts	2
Tolerance	M
Type of product	Indexable insert for turning