

Pneumatic random orbital sander, Type: R036CC2HL



Order data

Order number	079657 R036CC2HL
GTIN	663023170909
Item class	03I

Description

Version:

Powerful random orbital sanders with polyurethane hook and loop fastening backing pads. **Easy to use** due to light-weight composite housing and ergonomic hand application area. **Robust, smooth-running, and low-vibration pneumatic drive** with steel cylinder, low noise level.

Powerful random orbital sander for **external extraction system**. With a 2.5 mm orbital stroke.

Note:

See No. 567775 or 567901 for hook and loop grinding discs.

Technical description

maximum vibration to EN	3.9 m/s ²
maximum air consumption	498 l/min
Stroke	2.5 mm
maximum speed	13000 min ⁻¹
Backing pad Ø	150 mm
Operating noise	82 dB(A)
Type of extraction	External

Weight	0.8 kg
Power supply	Pneumatic
Type of product	Random orbital sander