

## Pneumatic random orbital sander, Type: 4152HLSR



### Order data

Order number	079657 4152HLSR
GTIN	663023066226
Item class	03I

### Description

#### Version:

Powerful random orbital sanders with polyurethane hook and loop fastening backing pads. **Easy to use** due to light-weight composite housing and ergonomic hand application area. **Robust, smooth-running, and low-vibration pneumatic drive** with steel cylinder, low noise level. Lightweight and reliable 75 mm random orbital sander for **external extraction system**. With a 2.5 mm orbital stroke.

#### Note:

See No. 567775 or 567901 for hook and loop grinding discs.

### Technical description

Stroke	2.5 mm
maximum vibration to EN	4.7 m/s <sup>2</sup>
maximum speed	12000 min <sup>-1</sup>
Type of extraction	External
Backing pad Ø	75 mm
maximum air consumption	430 l/min

Weight	0.8 kg
Operating noise	82 dB(A)
Power supply	Pneumatic
Type of product	Random orbital sander