

Pneumatic random orbital sander, Type: R036CS1HL



Order data

Order number	079657 R036CS1HL
GTIN	663023170978
Item class	03I

Description

Version:

Powerful random orbital sanders with polyurethane hook and loop fastening backing pads. **Easy to use** due to light-weight composite housing and ergonomic hand application area. **Robust, smooth-running, and low-vibration pneumatic drive** with steel cylinder, low noise level. Powerful random orbital sander with **integral extraction** for clean surfaces. With a 5 mm orbital stroke.

Note:

See No. 567775 or 567901 for hook and loop grinding discs.

Technical description

Type of extraction	Own dust extraction
maximum vibration to EN	3.9 m/s ²
maximum air consumption	498 l/min
Stroke	5 mm
Backing pad Ø	150 mm
Weight	0.9 kg
Operating noise	82 dB(A)

maximum speed

13000 min⁻¹

Type of product

Random orbital sander