



Line Light work lamp, Type: 750

Order data

Order number	081340 750
GTIN	5708997000557
Item class	08C

Description

Version:

The Line Light work lamp is formed of an extruded acrylic profile with an **integral lens** (beam dispersion angle 75°). It is thus exceptionally **sturdy and shock-resistant**. It is thus designed for use under the **harsh conditions** and reliably provides strong and concentrated light in any working area. With **battery for mobile use** with additional torch on the end (150 lumen).

With 24 V DC input for direct connection to the machine or via transformer No. 081342 to the 230 V mains power supply.

The lamp can be rotated in its housing to give lighting without dazzle.

Function:

IP20: No protection against penetration by foreign bodies with $\varnothing < 12$ mm, however touching should be avoided, and no protection against water.

IP67: Protected against intermittent immersion in water and protected against penetration by dust (dust-tight), also completely protected against touching.

Application:

For installation at the **workplace or in the vehicle**.

Supplied with:

Work light, 2 clips and fittings, end piece, cable entry / clamp, 2 connection sleeves.

Technical description

Power supply	Mains-powered
Illumination	550 lm
Number of LEDs	96
IP Index of Protection	IP 67
Lamp replaceable	no
Light output	7 W

Nominal voltage	230 V
Spread angle	75 degrees
ATEX zone	no
Head Ø	25 mm
Overall length	750 mm
Type of product	Desk lamp / workstation lamp

Accessories

Magnetic holder	081344
Sucker pad holder	081345