



Laser distance meter DISTO™, Type: X6



Order data

Order number	465550 X6
GTIN	7640180531258
Item class	47C

Description

Version:

Impact resistant plastic casing with easy-to-use keypad with symbols. High quality **Leica glass lens** in an particularly temperature-resistant and sturdy **magnesium casing**. Illuminated and rotating colour display for optimum legibility. Power Range Technologie™ for measurements **up to 150 m without target board**. Laser class 2 tested in accordance with ISO 16331-1.

Function:

IP65: Protected against jets of water from all directions and protected against penetration by dust (dust-tight), also completely protected against touching.

Supplied with:

Protective holder and wrist strap.

Note:

Data transfer via Bluetooth® Smart; also by smartphone using a Leica "DISTO™ Plan" app (Android from version 4.3, Apple from iPhone 4s). Easy generation of sketches.

Technical description

Digital target searcher with zoom	4-fold
Length	155 mm

Series	DISTO™
Width	68 mm
indirect measurements (Pythagoras)	yes
Addition/subtraction	yes
Minimum / maximum measurements	yes
Interface	Bluetooth interface
Weight	230 g
Clinometer	360 degrees
Type of rechargeable battery	Lithium-ion
IP Index of Protection	IP 65
Height	25 mm
Threaded socket for stand	1/4 UNC in
Measuring accuracy	±1.0 mm
Power supply	Li-ion
Recall last measurements	yes
Surface and volume calculations	yes
Range	250 m
multi-function endpiece	yes
Power supply	Mains operated
Reversible reading	mm / inch
Laser class to IEC 825–1	2
Type of product	Distance meter