


**TNMG 160408, Grade: CA4515**

**Order data**

Order number	251583 CA4515
GTIN	
Item class	25E

**Technical description**

Corner radius	0.8 mm
Cutting depth $a_p$	0.5 - 5 mm
Feed $f$	0.05 - 0.7 mm/rev.
Chip breaker	STD
Main application	K
Cutting conditions	slightly interrupted
Cutting speed $v_c$ main application	110 - 360 m/min
Grade	CA4515
Finishing/roughing assignment	Semi-roughing
Tool material	Carbide
ISO code indexable insert	TNMG 160408
Number of changes/inserts	6

Type of product

Indexable insert for turning