



**TNMG 160408, Grade: KW10**

**Order data**

Order number	251583 KW10
GTIN	4960664220861
Item class	25E

**Description**

TNMG 160408 KW10 Grade: KW10

Chip breaker: AH

Cutting depth  $a_p$ : 1 - 4 mm

Feed  $f$ : 0.1 - 0.35 mm/rev.

Cutting speed  $v_c$  main application: 60 - 400 m/min

**Technical description**

Main application	N
Cutting speed $v_c$ main application	60 - 400 m/min
Feed $f$	0.1 - 0.35 mm/rev.
Cutting conditions	slightly interrupted
Chip breaker	AH
Cutting depth $a_p$	1 - 4 mm
Corner radius	0.8 mm
Grade	KW10

Finishing/roughing assignment	Semi-roughing
Tool material	Carbide
ISO code indexable insert	TNMG 160408
Number of changes/inserts	6
Type of product	Indexable insert for turning