


DCMT 070208, Grade: CA525

Order data

Order number	260486 CA525
GTIN	4960664680085
Item class	25E

Description

DCMT 070208 CA525 Grade: CA525

Chip breaker: GK

Tolerance: M

Cutting depth a_p : 0.5 - 3 mm

Feed f : 0.1 - 0.3 mm/rev.

Cutting speed v_c main application: 80 - 330 m/min

Technical description

Corner radius	0.8 mm
Cutting conditions	slightly interrupted
Chip breaker	GK
Feed f	0.1 - 0.3 mm/rev.
Main application	P
Cutting speed v_c main application	80 - 330 m/min
Cutting depth a_p	0.5 - 3 mm

Grade	CA525
Finishing/roughing assignment	Skrubbearbejdning-sletbearbejdning
Tool material	Carbide
ISO code indexable insert	DCMT 070208
Number of changes/inserts	2
Tolerance	M
Type of product	Indexable insert for turning