

**Location device, Type: GMS120-27****Order data**

Order number	465570 GMS120-27
GTIN	4053423255331
Item class	46T

Description**Version:**

Reliable location even of buried objects up to 120 mm deep. Three detection modes (plasterboard, metal, live cables) for different applications. Reliable detection of objects, giving a visual and acoustic signal. Precise indication of the object centre. The centre point of the object that is sought can be simply marked using the marking aperture. Large illuminated display. Softgrip surface for a better grip.

Function:

IP54: Protected against splashed water from all directions and protected against penetration of dust into the inside (protected against dust), also completely protected against touching.

Application:

Detectable materials: Ferrous metals, non-ferrous metals, wooden frameworks, live cables.

Supplied with:

Battery No. 081551 size LR6, protective case.

Technical description

Detection depth steel	100 mm
Detection depth copper	120 mm

Detection depth wood	30 mm
IP Index of Protection	IP 54
Weight	270 g
Measuring range	120 mm
Power supply	Battery-powered
Width	113 mm
Height	78 mm
Length	208 mm
Article no of the battery / rechargeable battery fitted	081551 LR6
Detection depth live conductors	50 mm
Type of product	Location device