

**Cordless combi drill, Type: 71040761****Order data**

Order number	070100 71040761
GTIN	4014586898865
Item class	03F

Description**Version:****2-Speed cordless combi drill with brushless motor.**

- Electronic speed control for smooth, safe starts to drilling and screw driving; reversible.
- 2-speed all-metal gearbox with selectable hammer drive in metal, stone and masonry.
- Multi-stage torque adjustment and removable drill chuck.
- With QuickIN all-metal drill chuck (120 Nm) with carbide-coated jaws and high clamping forces.
- FEIN SafetyCell technology. Protects the battery and the machine against overheating and deep discharge.

Supplied with:**Without battery and without charger.**

Supplied with 1 pc. QuickIN drill chuck (120 Nm), 1 pc. belt clip, 1 pc. L-BOXX.

Note:

See No. 073851 – 073866 for suitable batteries and chargers.

Technical description

Motor design	Brushless
--------------	-----------

Packaging	Modular case (L-Boxx)
typical application	Heavy Duty
Manufacturer's designation	ASB 18 Q AS Select
maximum speed 1st speed	0 - 450 min ⁻¹
Weight	1.5 kg
maximum torque hard	60 Nm
Power supply	Rechargeable battery-powered
Type of rechargeable battery	Lithium-ion
maximum twist drill size Ø in wood	50 mm
maximum vibration to EN without hammer drill function	<2,5 m/s ²
maximum twist drill size Ø in concrete	13 mm
suitable battery - supplier / battery type / voltage	Bosch 18 V
Battery voltage	18 V
maximum twist drill size Ø in steel	13 mm
Number of rechargeable batteries contained	0
maximum vibration to EN with hammer drill function	130 m/s ²
maximum speed 2nd speed	2000 min ⁻¹
maximum torque soft	38 Nm
Quick-clamping chuck range	1.5 - 13 mm
Type of product	limpact drill /screwdriver