

Garant

Circular saw blade, double alternating flat teeth with chamfer Steel, Blade Ø D: 305mm



Order data

Order number	584006 305
GTIN	4067263117766
Item class	51S

Description

Version:

Tipped with carbide inserts, precision version with high-strength blade, noise damped. Generously dimensioned carbide teeth allow multiple re-grinding. With significantly longer tool life.

Application:

For cutting **stainless steel** with tenon saws and mitre saws. Problem-free cutting of mild steel profiles, pipes and plates. Low-burr, quick cutting without cooling.

Technical description

Blade Ø D	305 mm
Number of teeth	60
Bore Ø	25.4 mm
Width of cut B	2.2 mm
Tool material	Carbide

Suitable for material	Steel
Type of product	Circular saw blade