

**Garant**

**Circular saw blade, double alternating flat teeth with chamfer Steel, Blade Ø D: 305mm**

**Order data**

Order number	584006 305
GTIN	4067263117766
Item class	51S

**Description****Version:**

**Tipped with carbide inserts**, precision version with high-strength blade, noise damped. Generously dimensioned carbide teeth allow multiple re-grinding. With significantly longer tool life.

**Application:**

For cutting **stainless steel** with tenon saws and mitre saws. Problem-free cutting of mild steel profiles, pipes and plates. Low-burr, quick cutting without cooling.

**Technical description**

Blade Ø D	305 mm
Number of teeth	60
Suitable for materials	Steel
Bore Ø	25.4 mm
Width of cut B	2.2 mm

