

Garant

Torque screwdriver with 1/4 inch bit holder, with scale, automatic triggering, maximum torque: 600cNm



Order data

Order number	659100 600
GTIN	4067263117193
Item class	61E

Description

Version:

- **Ergonomically shaped power grip with easy-grip Haptoprene surface ensures high transmission of force.**
- **Clear and easy to read thanks to large numeric display.**
- **Short 36° trigger distance with clearly audible and perceptible signal.**
- **Trigger mechanism with 10 detent elements made of high-alloy tool steel with high wear resistance for a long service life.**
- **The overload clutch ("Slipper") ensures the set value is not exceeded.**
- **Easy to use and easy to identify the locked and unlocked state by the orange signal ring on the rotary knob.**
- **Bit holder (1/4 inch – D 6.3 / F 6.3) with quick release fastener. Fast bit changes with one hand.**

Function:

On reaching the set torque value, the screwdriver can be felt and heard to trigger and is then again immediately ready for use. In the anti-clockwise direction of rotation: without torque function to loosen screw connections.

Standard:

Tested to **DIN EN ISO 6789**.

Accuracy:

±6 %.

Technical description

Data can be recorded	no
----------------------	----

Data sheet

Torque measuring accuracy	±6 %
maximum torque	600 cNm
Resolution	10 cNm
Direction of tightening	Right-hand tightening
Overall length L	204 mm
Weight	310 g
Bit socket	D 6.3
Bit socket	F 6.3
Torque range	100 - 600 cNm
Trigger principle	mechanical slip clutch
Measurement process	Torque
Reversible reading	cNm
Calibration	O1
Setting the trigger value	with adjustment scale
Release signalling	acoustic
Release signalling	haptic
Measurement technology	mechanical
Adjustable trigger value	adjustable
Standard	DIN EN ISO 6789
Display	analogue
Feedback	acoustic signal
Feedback	triggering
Connection format	Bit holder 1/4 inch
Test certificate	Manufacturer's test certificate
Torque fixed setting	yes
Type of product	Torque screwdriver

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/659100-600>

