

Garant

GARANT Master Steel solid carbide high-performance drill DIN 6535 HA, TiAlN, Ø DC h7: 6,2mm



Order data

| | |
|--------------|---------------|
| Order number | 122761 6,2 |
| GTIN | 4067263121480 |
| Item class | 11E |

Description

Version:

Robust drill design and optimised special point geometry for the **best possible chip formation and reliable chip breakage** with **higher feed rates at the same time**. **Advanced micro-geometry, convex cutting edge** and **relieved coneto** provide additional stability for the main cutting edge. **Optimised flute geometry and patented face geometry** for **reliable chip evacuation** in steel materials and cast material. **High-performance coating** of the latest generation.

Note:

Flute length $L_c = L_2 + 1.5 \times D_c$.

HB and HE shanks are available at the same price as HA.

HB shanks: order with **No. 122762**.

For **HE shanks:** use order **No. 122761 + 129100HE**.

Technical description

| | |
|------------------------------------------|---------|
| Number of cutting edges Z | 2 |
| Flute length L_c | 53 mm |
| Tolerance nominal Ø | h7 |
| Shank Ø D_s | 8 mm |
| Overall length L | 91 mm |
| Nominal Ø D_c | 6.2 mm |
| recommended maximum drilling depth L_2 | 43.7 mm |

| | |
|------------------------------------------|-------------------|
| Standard | DIN 6537 |
| Feed f in steel < 1100 N/mm ² | 0.21 mm/rev. |
| Series | Master Steel |
| Coating | TiAlN |
| Tool material | Solid carbide |
| Version | 6×D |
| Point angle | 140 degrees |
| Shank | DIN 6535 HA to h6 |
| Through-coolant | yes, with 25 bar |
| Machining strategy | HPC |
| Semi-Standard | yes |
| Colour ring | green |
| Type of product | Jobber drill |

User data

| | Suitability | V _c | ISO code |
|--------------------------------|-------------------------------------------|----------------|----------|
| Steel < 500 N/mm ² | suitable | 170 m/min | P |
| Steel < 750 N/mm ² | suitable | 155 m/min | P |
| Steel < 900 N/mm ² | suitable | 145 m/min | P |
| Steel < 1100 N/mm ² | suitable | 130 m/min | P |
| Steel < 1400 N/mm ² | suitable | 110 m/min | P |
| Steel < 55 HRC | suitable | 60 m/min | H |
| INOX < 900 N/mm ² | suitable only under restricted conditions | 55 m/min | M |
| INOX > 900 N/mm ² | suitable only under restricted conditions | 45 m/min | M |
| GG | suitable | 130 m/min | K |
| GGG | suitable | 90 m/min | K |
| Uni | suitable | | |

| | |
|-------------|----------|
| wet maximum | suitable |
| wet minimum | suitable |
| Air | suitable |