

LOCTITE.
Glue, Type: 3450**Order data**

Order number	083260 3450
GTIN	5010266007694
Item class	04L

Description**Version:**

5-minute 2-component epoxy adhesive (1:1) 25ml

Thee 2-component epoxy resin adhesive cures at room temperature after mixing. It develops high strength on metal surfaces. The crack-filling characteristics of the adhesive system make it suitable for rough and badly fitting surfaces of metal, ceramic, thermoplastics and wood.

hazardous goods class: 9

Chemical basis: Epoxy resin

Operating temperature range: -55 °C

Touch dry after: 4 - 6 min

Tensile shear strength: 25 N/mm²

Colour: grey

Capacity: 25 g

Technical description

Tensile shear strength	25 N/mm ²
Manufacturer's designation	LOCTITE EA 3450
Dynamic viscosity	35000 mPa·s

UN number	UN3082
Capacity	25 g
Processing time	300 s
Hardness according to Shore A	68
Processing temperature	-2 - 22 °C
Storage temperature	8 - 21 °C
Chemical basis	Epoxy resin
Operating temperature range	-55 °C
Working life after date of manufacture	24 mo
hazardous goods class	9
Suitable for material	Metal
Colour	grey
Shape	Paste
Density	1.7 g/cm ³
Functional strength to	15 min
Touch dry after	4 - 6 min
Maximum gap size	5 mm
Type of product	Two-component adhesive