

REMS

Pipe-threading tool "EVA Set R" complete with sheet steel case, Type: 1/2-1.1/4



Order data

Order number	820301 1/2-1.1/4
GTIN	4039976048361
Item class	84B

Description

Version:

Quick cutting head change due to easy insertion into the ratchet head with quick-release lock. Cutting heads with long pipe guide and exactly set threading dies. The dies are particularly wear-resistant and easy to exchange. Ratchet reversible for right- and left-hand threads. The threading dies can be reversed for thread cutting right up to a wall (for short pipe ends that are already in place). Not suitable for stainless steel pipes.

Application:

A handy and light die stock for use on building sites. **The small head Ø permits working in confined places.**

Suitable for:

Whitworth pipe thread to DIN EN 10226 **taper 1:16.**

Content:

associated cutting heads 1 pc. each
(for Whitworth pipe thread): 1/2; 3/4; 1; 1.1/4 inch;
Ratchet arm: 1 pc.

Note:

The following items are also available as individual parts on request:

- **Ratchet arm.**
- **Complete cutting heads with jaws, as well as spare jaws.**

When ordering please state the desired size.

Technical description

Number of ratchet arms	1
Whitworth pipe threading head	1/2; 3/4; 1; 1.1/4 in
Standard	DIN EN 10226
Packaging	Sheet metal case
Type of product	Pipe-threading tool

Accessories

Ratchet arm "Central" Type C1.1/4	820600 C1.1/4
Cutting head with jaws Thread type R1	820650 R1
Carrying box of sheet steel for pipe-threading tool "Central" Type C1.1/4	820620 C1.1/4
Cutting head with jaws Thread type R1.1/4	820650 R1.1/4
Cutting head with jaws Thread type R1/2	820650 R1/2
Cutting head with jaws Thread type R3/4	820650 R3/4