



Digital rebound hardness tester1



Order data

Order number	495024 1
GTIN	2050002078604
Item class	49G

Description

Version:

Sturdy casing of anodised aluminium. Evaluation to DIN 50156 and ASTM A956 in Rockwell HRC and HRB, Vickers HV, Brinell HB, and the tensile strength of steel. The device can be used in any orientation (horizontal, facing upwards, facing downwards...). Internal memory for >1,000,000 measurement values, USB port for data transmission to a USB stick.

Accuracy:

±4 HL (0.5 % at 800 HL).

Supplied with:

Impact tool type D, hardness comparison block, USB data cable, cleaning brush, transport case, charger, and manufacturer's certificate.

Optional extras:

Alignment rings for curved surfaces, test blocks with DAkkS certificate and impact tools types DC, DL, D+15, C and G on request.

Spare part:

Connecting cable to impact measuring tool 495023.

Technical description

Weight	430 g
--------	-------

Data sheet

Minimum weight of test piece	2.5 kg
Width	84 mm
Length	154 mm
Height	23 mm