

Garant GRIDLINE

ESD tool cabinet complete with drawers 50 kg, 36×24G, Height mm / number of drawers: 800/6**Order data**

Order number	972460 800/6
GTIN	4067263126539
Item class	9GK

Description**Version:**

Tool cabinet **ESD conductive**, to DIN EN 61340-5-1. Completely equipped tool cabinet in 40×28G, with drawers 36×24G. Cabinet can be centrally locked by a cylinder lock. Can be locked centrally with a cylinder lock. **100% full extension drawers** with differential runners. Drawers with slots at 25-mm intervals to take slotted dividers (from drawer front height 75 mm). An anti-tilt device prevents more than one drawer being opened at one time.

Includes ESD grounding cable.

Colour:

Body and drawer body light grey similar to RAL 7035 **ESD powder-coated.**

Note:

- **When lifting and transporting the cabinet, make sure the drawers are well secured within the casing.**
- **All plastic components (e.g. covering caps and handles) are non-ESD conductive.**

Technical description

Drawer usable area in G	36×24
Height	800 mm
Drawer usable width in G	36

Weight	138 kg
Usable height	700 mm
Drawer usable width	900 mm
Drawer usable depth	600 mm
Width	1000 mm
Drawer usable depth in G	24
Depth	700 mm
Drawer/pull-out shelf load capacity	50 kg
Drawer runner extension (partial/full extension)	100 %
Drawer runner extension	Anti-tilt lock
Height adjustment interval	25 mm
Cylinder lock	modular barrel
electrostatic characteristic	EGB/ESD
Product name attribute	36x24G
Type of product	Tool cabinet

Accessories

Lock plate for GridLine Type HU21	914227 HU21
ESD tool cabinet casing for drawers Height 800 mm	972470 800
ESD drawer Drawer front height 100 mm	972473 100
ESD drawer Drawer front height 150 mm	972473 150
ESD drawer Drawer front height 200 mm	972473 200
ESD drawer Drawer front height 75 mm	972473 75