

Garant
GARANT Master TM plain shank thread mill with countersink 2×D, AlTiN, UNF: 10-32

Order data

Order number	139738 10-32
GTIN	4067263126959
Item class	11D

Description
Version:

Solid carbide thread milling cutters **with irregular cutting edge spacing and an increased number of cutting edges**. Due to the **irregular cutting edge spacing** they achieve very **smooth running** and **long tool life**.

Newly developed universal geometry and **high-performance coating** for use across a wide spectrum of materials.

- **Significantly reduced vibration due to irregular cutting edge spacing.**
- **Corrected thread profile for avoidance of profile distortions.**
- **Increased number of cutting edges.**
- **The latest generation of AlTiN-based HiPIMS coating.**
- **increased number of cutting edges**
- **new coating for optimum wear resistance**

Advantage:

Incorporating a countersink profile for a 90° countersink and thread milling in a single operation.

Application:

For **UNF unified fine threads** ASME-B1.1.

Note:

HB and HE shanks are available at the same price as HA

Order **HB** shank: with **No. 139738 + 129100 HB**

Order **HE** shank: with **No. 139738 + 129100 HE**

Technical description

Thread Ø	4.83 mm
----------	---------

Threads per inch	32
Shank length L_s	36.8 mm
Neck $\varnothing D_1$	5.5 mm
Shank $\varnothing D_s$	6 mm
Thread pitch	0.794 mm
Number of clamping slots	4
Feed f_z in steel $< 750 \text{ N/mm}^2$	0.04 mm
Nominal $\varnothing D_c$	3.81 mm
Thread type	UNF
Thread type	UNF-LH
Flute length L_c	9.1 mm
Thread size	10-32 UNF
Programming value for countersink L_1	9.86 mm
Overall length L	58 mm
No. of teeth Z	4
Series	Master TM
Coating	AlTiN
Flank angle	60 degrees
Tool material	Solid carbide
Shank	DIN 6535 HA to h6
Through-coolant	yes
Cutting direction	right-hand
Application for type of drilling	up to $2 \times D$ for blind holes
Application for type of drilling	up to $2 \times D$ for through holes
Spacing of the cutters	unequal spacing
Countersink angle	90 degrees
Shank tolerance	h6
Colour ring	green
Internal/external application	Internal

Type of product

thread milling cutter

User data

	Suitability	V_c	ISO code
Alu plastics	suitable	220 m/min	N
Aluminium (short chipping)	suitable	220 m/min	N
Alu > 10% Si	suitable	180 m/min	N
Steel < 500 N/mm ²	suitable	140 m/min	P
Steel < 750 N/mm ²	suitable	130 m/min	P
Steel < 900 N/mm ²	suitable	120 m/min	P
Steel < 1100 N/mm ²	suitable	90 m/min	P
Steel < 1400 N/mm ²	suitable	80 m/min	P
Steel < 50 HRC	suitable only under restricted conditions	45 m/min	H
TOOLOX 33	suitable	85 m/min	H
TOOLOX 44	suitable	50 m/min	H
INOX < 900 N/mm ²	suitable	82 m/min	M
INOX > 900 N/mm ²	suitable	75 m/min	M
Ti > 850 N/mm ²	suitable	50 m/min	S
GG(G)	suitable	120 m/min	K
CuZn	suitable	200 m/min	N
Uni	suitable		
wet maximum	suitable		
wet minimum	suitable		
Air	suitable		

Services

Shank grinding Type HB

129100 HB

Shank grinding Type HE

129100 HE

