

**Garant**
**Vibratory finishing machine (2 litres) with separating station, Type: GMT2**

**Order data**

Order number	501310 GMT2
GTIN	4067263130741
Item class	51B

**Description**
**Version:**

**Vibratory finishing machine GMT2** in **compact design**, for automated finishing work on **small to medium batch sizes**.

- **Powerful motor with defined speed range.**
- **Steel trough (2 l) with polyurethane coating.**
- **Removable separating station for manually separating the workpiece and grinding medium.**
- **Effortless separation thanks to ergonomic tipping mechanism.**
- **Intuitive to control via control panel with timer function.**
- **Quiet, dust-free working thanks to transparent cover.**

**Application:**

The preferred choice for **deburring turned and milled parts** and **3D-printed** workpieces.

Suitable for **metals** and **plastics**. This machine can also handle the subsequent step of **polishing**. **Only dry machining is recommended (no compound required).**

**Supplied with:**

1 pc. vibratory finishing machine with control panel and removable separating station 1 pc. separating screen with 10 mm hole grid 1 pc. separating screen with 18 mm hole grid 1 pc. ceramic grinding bodies (3 kg), triangular, coarse (No. 501505 0606T) 1 pc. ceramic grinding bodies (3 kg), triangular (oblique), coarse (No. 501515 1015TA) 1 pc. ceramic grinding bodies (3 kg), cylinder (oblique), coarse (No. 501525 0305CA) 1 pc. porcelain grinding bodies (3 kg), cylinder (oblique), polishing (No. 501585 0406CA) 1 pc. storage box (No. 964486 EF4070) 1 pc. GARANT GreenPlus Flex Cleaner 500 ml (No. 088001 500) 1 pc. 3M high-performance cleaning cloth (No. 089190 BLUE)

## Technical description

Speed range	3000 min <sup>-1</sup>
Mains frequency	50 Hz
Volume of trough	2 l
Inner depth of trough D <sub>2</sub>	85 mm
Width of machine W <sub>1</sub>	400 mm
Length of machine L <sub>1</sub>	750 mm
Power consumption	50 W
AC supply voltage	230 V
Inner Ø of trough	100 mm
Outer Ø of trough	220 mm
Height of machine	285 mm
Total weight	20 kg
Type of product	Vibratory finishing machine