

**HOLEX®**
**DCMT 11T304 Set 10 pieces, Grade: HBX130**

**Order data**

Order number	260505 HBX130
GTIN	4045197670069
Item class	22D

**Description**

DCMT 11T304 Set of 10 pieces HBX130 Grade: HBX130

Chip breaker: MM

Cutting depth  $a_p$ : 0.1 - 3.75 mm

Feed  $f$ : 0.06 - 0.36 mm/rev.

Cutting speed  $v_c$  main application: 60 - 200 m/min

**Technical description**

Cutting conditions	slightly interrupted
Corner radius	0.4 mm
Chip breaker	MM
Feed $f$	0.06 - 0.36 mm/rev.
Main application	M
Cutting depth $a_p$	0.1 - 3.75 mm
Cutting speed $v_c$ main application	60 - 200 m/min

Grade	HBX130
Finishing/roughing assignment	Finishing
Tool material	Carbide
ISO code indexable insert	DCMT 11T304
Number of changes/inserts	2
Type of product	Indexable insert for turning