


Garant

GARANT Master Steel SlotMachine solid carbide roughing end mill HPC, TiAlN, Ø d11 DC: 10mm



Order data

Order number	GG1050 10
GTIN	4067263134947
Item class	GGN

Description

Version:

With a new-type knurled profile, optimised for higher feed rates. Improved cutting edge protection thanks to slight edge honing. Tremendous bending strength due to the use of ultra-fine grain substrate.

Feed rate per tooth up to 0.1 mm up to a depth of 2×D (in the slot milled from solid).

Same as 205550.

Advantage:

The tool geometry produces particularly tightly rolled swarf that is discharged via flat chip breaker recesses. As a result, the tool maintains an extremely stable core. Plunge angle of up to 10° possible thanks to generous recess on the front face.

Application:

For roughing machining, particularly suitable for full-slot machining.

Technical description

Helix angle	42 degrees
Cutting edge Ø D _c	10 mm
Direction of infeed	horizontal, oblique and vertical

Shank $\varnothing D_s$	10 mm
Overall length L	72 mm
Overhang length L_1 incl. recess	30 mm
Feed f_z for side milling in steel < 900 N/mm ²	0.09 mm
Recess $\varnothing D_1$	9.3 mm
No. of teeth Z	5
Corner chamfer width at 45°	0.5 mm
Feed f_z for slot milling in steel < 900 N/mm ²	0.065 mm
Tolerance nominal \varnothing	d11
Flute length L_c	22 mm
Shank	DIN 6535 HB to h6
Corner chamfer angle	45 degrees
Series	Master Steel
Coating	TiAlN
Tool material	Solid carbide
Standard	DIN 6527
Milling profile	NR
Spacing of the cutters	unequal spacing
Cutting width a_e for milling operation	0.3×D for side milling
Cutting width a_e for milling operation	0.3×D for side milling
Through-coolant	no
Machining strategy	HPC
Colour ring	green
Type of product	End / face mill

User data

	Suitability	V_c	ISO code
Steel < 500 N/mm ²	suitable	200 m/min	P
Steel < 750 N/mm ²	suitable	180 m/min	P

Steel < 900 N/mm ²	suitable	160 m/min	P
Steel < 1100 N/mm ²	suitable	140 m/min	P
Steel < 1400 N/mm ²	suitable	110 m/min	P
INOX < 900 N/mm ²	suitable	50 m/min	M
INOX > 900 N/mm ²	suitable	35 m/min	M
GG(G)	suitable	200 m/min	K
Uni	suitable		
wet maximum	suitable		
wet minimum	suitable only under restricted conditions		
dry	suitable		
Air	suitable		

Accessories

GARANT Master Steel SlotMachine solid carbide roughing end millHPC Ø d11 DC 10 mm

205550 10