


**Value pack HOLEX Clever Tap machine tap Form B DIN 371/376, M: M8****Order data**

Order number	GG1271 M8
GTIN	4067263134695
Item class	GGN

**Description****Version:****Same as No. 131265.****With spiral point.****HOLEX Clever Tap:**

Sturdy tap for conventional standard applications. High-quality HSS-E tool material and geometry for steels. Surface: Bronze-coloured tempered thread profile. **ISO 2 6H**

**HSS-E****Technical description**

Thread type	M
Shank $\varnothing D_s$	8 mm
Number of cutting edges Z	3
Shank square $\square$	6.2 mm
Number of clamping slots	3
Thread depth	16 mm
Overall length L	90 mm

Thread size	M8
Thread Ø	8 mm
Tool material	HSS E
Standard	DIN 371
Tolerance class	ISO 2 6H
Tapping hole Ø	6.8 mm
Thread pitch	1.25 mm
Coating	uncoated
Flank angle	60 degrees
Thread standard	DIN 13
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	right-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Series	CleverTap
Type of product	Taps

## User data

	Suitability	V <sub>c</sub>	ISO code
Aluminium	suitable only under restricted conditions	13 m/min	N
Aluminium (short chipping)	suitable only under restricted conditions	13 m/min	N
Steel < 500 N/mm <sup>2</sup>	suitable	12 m/min	P
Steel < 750 N/mm <sup>2</sup>	suitable	12 m/min	P

Steel < 900 N/mm <sup>2</sup>	suitable only under restricted conditions	6 m/min	P
Oil	suitable		
wet maximum	suitable		

---

## Accessories

HOLEX Clever Tap machine tapForm B DIN 371/376 M M8	131265 M8
---	-----------