

**HOLEX Clever Tap machine tap Form B DIN 371/376, uncoated, M: M6****Order data**

Order number	GG1271 M6
GTIN	4067263134688
Item class	GGN

Description**Version:****Same as No. 131265.****With spiral point.****HOLEX Clever Tap:**

Sturdy tap for conventional standard applications. High-quality HSS-E tool material and geometry for steels. Surface: Bronze-coloured tempered thread profile. **ISO 2 6H**

HSS-E**Technical description**

Overall length L	80 mm
Thread size	M6
Thread pitch	1 mm
Number of cutting edges Z	3
Thread depth	12 mm
Shank $\varnothing D_s$	6 mm
Thread \varnothing	6 mm

Shank square □	4.9 mm
Tool material	HSS E
Number of clamping slots	3
Tolerance class	ISO 2 6H
Standard	DIN 371
Tapping hole Ø	5 mm
Thread type	M
Coating	uncoated
Flank angle	60 degrees
Thread standard	DIN 13
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	right-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Series	CleverTap
Type of product	Taps

User data

	Suitability	V _c	ISO code
Aluminium	suitable only under restricted conditions	13 m/min	N
Aluminium (short chipping)	suitable only under restricted conditions	13 m/min	N
Steel < 500 N/mm ²	suitable	12 m/min	P
Steel < 750 N/mm ²	suitable	12 m/min	P

Steel < 900 N/mm ²	suitable only under restricted conditions	6 m/min	P
Oil	suitable		
wet maximum	suitable		

Accessories

HOLEX Clever Tap machine tapForm B DIN 371/376 M M6	131265 M6
---	-----------