

metabo**Angle grinder, Type: 613052840****Order data**

Order number	P07004 613052840
GTIN	4061792205369
Item class	03D

Description**Version:**

- **New generation of brushless cordless angle grinder: as powerful as a 1100-watt plug-in tool thanks to 40% more power**
- **Maintenance-free brushless motor with maximum efficiency and an extremely easy to handle design**
- **Protective hood that can be adjusted without tools; can be fixed in a twist-proof manner**
- **Battery pack can be turned in 90° steps for best ergonomics in every working position**
- **Metabo S-automatic mechanical safety clutch: Minimises kick-back when the disc jams unexpectedly to the lowest level on the market – for maximum user protection**
- **Electronic overload protection, soft start and restart protection**
- **Many brands, one battery system: This product can be combined with all 18 V battery packs and chargers of the CAS brands: www.cordless-alliance-system.com**

Supplied with:

Protective hood, support flange, twin-hole nut, additional handle, two-pin wrench, without battery pack and without charger.

Technical description

maximum vibration to EN	8 m/s ²
No load speed	10000 min ⁻¹
Battery voltage	18 V

maximum disc Ø	125 mm
Connection thread	M14
Manufacturer's designation	W 18 LT BL 11-125
maximum cutting depth	33 mm
Power supply	Mains operated
Packaging	cardboard
Weight	1.8 kg
Operating noise	92 dB
Type of product	Angle grinder