


Garant
GARANT Master Eco SET HB7130-2, left-hand, Shank size: 20mm

Order data

| | |
|--------------|---------------|
| Order number | 255163 20 |
| GTIN | 4067263134091 |
| Item class | 29W |

Description
Supplied with:

1 pc. lever lock toolholder No. 250001 and 40 pcs. indexable inserts No. 250158 HB7130-2.

Technical description

| | |
|---------------------------------|-------------------------------|
| Functional width L ₄ | 25 mm |
| Standard | Works standard |
| Standard | DIN ISO 5610 |
| Head length L ₁ | 30 mm |
| suitable indexable insert | CN.. 1204.. |
| Overall length L | 90 mm |
| Shank size | 20 mm |
| ISO code toolholder | PCLNR/L 2020X12 |
| Application type | left-hand |
| Through-coolant | yes |
| Setting angle κ | 95 degrees |
| Application | External longitudinal turning |

| | |
|-----------------|-------------------------------|
| Application | External longitudinal turning |
| Type of product | Screw-on toolholder |