

HOLEX
Rough grinding disc "2 in 1", Disc Ø×disc width / quantity: 125X6/100mm


Order data

| | |
|--------------|------------------|
| Order number | GG5050 125X6/100 |
| GTIN | 4067263133247 |
| Item class | GGN |

Description

Version:

Open homogeneous structure; low odour grinding; glass fibre reinforcing fabric for maximum work safety; cool grinding; bore Ø 22.23 mm. The iron, sulphur and chlorine content are less than 0.1 %, making them suitable for working stainless steels (INOX). For use on electric and pneumatic angle grinders.

- **Grit, bonding, abrasive additives as well as reinforcement of the rough grinding discs are optimised for maximum metal removal rate and working life in their respective applications.**
- **Shapes: Rough grinding discs, depressed centres (shapes 27, 28, 29)**
- **Grinding angle 20° to 30°**
- **Application: On electric and pneumatic angle grinders with maximum 80 m/s circumferential speed for grinding welds, surfaces, and edges.**

Rough grinding disc for **steel and stainless steel** with **long working life** and high metal removal rate.

Specification:

A30Q-BF (same as 560500) for steel and stainless steel with long working life and high metal removal rate.

Note:

Only sold in bulk pack quantities, not supplied individually. Ordering information: 1 set = 1 bulk pack.

Technical description

| | |
|---|---------------------|
| Contents | 100 |
| Disc thickness | 6 mm |
| Bore Ø | 22.23 mm |
| Disc Ø | 125 mm |
| Grinding medium code | A |
| Specification | A30Q-BF |
| Iron, sulphur and chlorine constituents | < 0.1 % |
| recommended approach angle | 20-30 degrees |
| optimised for material | INOX |
| optimised for material | Steel |
| maximum circumferential speed | 80 m/s |
| Type of product | Rough grinding disc |

User data

| | Suitability | V_c | ISO code |
|--------------------------------|---|-------|----------|
| Alu Mg | suitable only under restricted conditions | | |
| Steel < 900 N/mm ² | suitable | | |
| Steel < 1400 N/mm ² | suitable | | |
| Steel < 55 HRC | suitable | | |
| Steel < 60 HRC | suitable | | |
| Steel < 67 HRC | suitable only under restricted conditions | | |
| INOX | suitable only under restricted conditions | | |
| Ti | suitable only under restricted conditions | | |
| GG(G) | suitable only under restricted conditions | | |

| | |
|--------------|---|
| CuZn | suitable only under restricted conditions |
| Plastic, GRP | suitable only under restricted conditions |
| dry | suitable |

Accessories

| | |
|--|--------------|
| Rough grinding disc"2 in 1" Disc Ø×disc width 125X6 mm | 560500 125X6 |
|--|--------------|