

Garant GRIDLINE

**Pull-out frame for hanging goods 200 kg, 26×20G, Type: 90****Order data**

Order number	998260 90
GTIN	4067263136026
Item class	91R

**Description****Version:**

Pull-out frame with **100% full extension and differential runners**. Open in front, shell height at sides 46 mm, installation height 100 mm. With 4 cross tubes. Aluminium handle with labelling strips that can be exchanged and rewritten. With one-handed individual drawer release system.

**Suitable for:**

Drawer/shelf combination units, container equipment.

**Supplied with:**

Pull-out frame each complete with 1 pair drawer runner rails.

**Colour:**

RAL 7035 light grey **powder-coated**.

**Note:**

Not compatible with tool cabinets from group 93, can only be installed in drawer/shelf combination units.

**Technical description**

Individual drawer release system	One-hand
Usable width in G	26
Weight	31 kg
Installation height	90 mm
Usable depth in G	20
Drawer usable area in G	26×20
Application range	Container equipment

Total load capacity	200 kg
Drawer/pull-out shelf load capacity	200 kg
Drawer runner extension (partial/full extension)	100
Height adjustment interval	25 mm
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	26x20G
Usable width	650 mm
Usable depth	500 mm
Type of product	Pull-out shelf