



Digital XTL bore gauge with Bluetooth, Measurement range: 8-10mm



Order data

Order number	428761 8-10
GTIN	2050002078093
Item class	46B

Description

Version:

3-point bore gauges for blind hole measurement from size 12.5–16. Fixed carbide measuring jaws, from size 12.5–16 with carbide inserts. Large, sharp contrast digital display. Reliable measurement without a vernier. Excellently suitable for measuring vertical holes.

Function:

- **mm / inch selection.**
- **Setting 2 preset values.**
- **On / Off data storage button.**

Supplied with:

Measuring lever, micrometer head with UKAS test certificate, 1 battery No. 081560 size CR2032.

Optional extras:

Data cable No. 498950 (from size 20), No. 498951 (up to size 20), setting rings No. 484030, extensions No. 428510.

Technical description

Error limit	0.004 mm
Standard measuring depth	58 mm

Data sheet

Article no of the battery / rechargeable battery fitted	081560 CR2032
Measuring depth with extension	121 mm
Scale divisions	0.001 mm
Power supply	Battery-powered
Number of batteries contained	1
Dimension a	1.9 mm
Measuring range	8 - 10 mm
Standard	DIN 863
Reversible reading	mm / inch
Interface	RS232C interface
Interface	USB interface
Interface	Bluetooth interface
Measurement technology	digital
Packaging	sturdy box
Calibration	B6
Type of product	3-point bore gauge

Services

DAkkS calibration 3-point internal micrometer maximum measuring range 200 mm	022510 200
Calibration 3-point internal micrometer maximum measuring range 20 mm	022500 20

Accessories

Setting ring DIN 2250 C Nominal size \varnothing 9 mm	484030 9
Setting ring DIN 2250 C Nominal size \varnothing 8 mm	484030 8
Connection cable Duplex Type R2	498951 R2
Button cell / special battery Battery type CR2032	081560 CR2032
Extension for internal micrometers Type 1/63	428510 1/63

Setting ring DIN 2250 C Nominal size Ø 10 mm	484030 10
Connection cable Duplex Type USB2	498951 USB2