

**Garant****Abrasive flap disc speed+ CER, flat, Ø 125 mm, Grit: 40****Order data**

Order number	GG5239 40
GTIN	4067263136699
Item class	GGN

**Description****Version:**

- **High-quality self-sharpening ceramic grit (CER) for maximum abrasive power and low contact pressure.**
- **Active coating for cool cutting.**
- **Sturdy poly-cotton mixed fabric for ideal wear characteristics and stability, even when used on edges.**
- **Ergonomic and vibration-damping polyester plastic backing pad (can be reset).**
- **Best results on high-power angle grinders.**

**speed+** - optimised flap strip arrangement, for effectiveness similar to a fibre disc with **highly aggressive characteristics**.

Corresponds to 565239.

**Application:**

Edge smoothing, material removal.

**Technical description**

Bore Ø	22.23 mm
Contents	100

Grit	40
Disc Ø	125 mm
Shape description	flat
Grinding media	Ceramic grit (CER)
Grinding medium code	Ceramic
abrasive, cooling coating	yes
Iron, sulphur and chlorine constituents	< 0,1 %
Product name attribute	Ø 125 mm
optimised for material	INOX
maximum circumferential speed	80 m/s
Type of product	Abrasive flap disc

## User data

	Suitability	V <sub>c</sub>	ISO code
Alu Mg	suitable only under restricted conditions		
Steel < 900 N/mm <sup>2</sup>	suitable		
Steel < 1400 N/mm <sup>2</sup>	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable		
INOX	suitable		
Ti	suitable		
GG(G)	suitable		
CuZn	suitable only under restricted conditions		
Uni	suitable		
dry	suitable		

## Accessories

Abrasive flap discspeed+ CER, flat Grit 40

565239 40