



## Digital XTL bore gauge with Bluetooth, Measurement range: 10-12,5mm



### Order data

Order number	428761 10-12,5
GTIN	2050002078147
Item class	46B

### Description

**Version:**

**3-point bore gauges** for blind hole measurement from size 12.5–16. Fixed carbide measuring jaws, from size 12.5–16 with carbide inserts. Large, sharp contrast digital display. Reliable measurement without a vernier. Excellently suitable for measuring vertical holes.

**Function:**

- **mm / inch selection.**
- **Setting 2 preset values.**
- **On / Off data storage button.**

**Supplied with:**

Measuring lever, micrometer head with UKAS test certificate, 1 battery No. 081560 size CR2032.

**Optional extras:**

Data cable No. 498950 (from size 20), No. 498951 (up to size 20), setting rings No. 484030, extensions No. 428510.

### Technical description

Measuring range	10 - 12.5 mm
Number of batteries contained	1

Power supply	Battery-powered
Measuring depth with extension	134 mm
Standard measuring depth	58 mm
Scale divisions	0.001 mm
Article no of the battery / rechargeable battery fitted	081560 CR2032
Error limit	0.004 mm
Dimension a	1.9 mm
Standard	DIN 863
Reversible reading	mm / inch
Interface	RS232C interface
Interface	USB interface
Interface	Bluetooth interface
Measurement technology	digital
Packaging	sturdy box
Calibration	B6
Type of product	3-point bore gauge

### Services

DAkkS calibration 3-point internal micrometer maximum measuring range 200 mm	022510 200
Calibration 3-point internal micrometer maximum measuring range 20 mm	022500 20

### Accessories

Connection cable Duplex Type R2	498951 R2
Connection cable Duplex Type USB2	498951 USB2
Setting ring DIN 2250 C Nominal size Ø 10 mm	484030 10
Extension for internal micrometers Type 2/76	428510 2/76
Setting ring DIN 2250 C Nominal size Ø 11 mm	484030 11

## Data sheet

Button cell / special battery Battery type CR2032	081560 CR2032
Setting ringDIN 2250 C Nominal size Ø 12 mm	484030 12