



Digital XTL internal quick measuring set with Bluetooth, Measurement range: 6-10mm



Order data

Order number	428771 6-10
GTIN	2050002078130
Item class	46B

Description

Version:

3-point XT internal micrometer series for blind hole measurement from size 12.5–16. Fixed carbide measuring jaws, from size 12.5–16 with carbide inserts. Large, sharp contrast digital display. Reliable measurement without a vernier. Excellently suitable for measuring vertical holes.

Function:

- mm / inch selection.
- Setting 2 preset values.
- On / Off data storage button.

Supplied with:

Digital internal micrometers No. 428760 and setting rings with UKAS test certificate.

Technical description

Setting ring \varnothing	8 mm
Scale divisions	0.001 mm
Error limit	0.004 mm

Data sheet

Number of measuring heads	2
Number of batteries contained	1
Measuring range	6 - 10 mm
Power supply	Battery-powered
Article no of the battery / rechargeable battery fitted	081560 CR2032
Standard	DIN 863
Reversible reading	mm / inch
Interface	RS232C interface
Interface	USB interface
Interface	Bluetooth interface
Measurement technology	digital
Packaging	sturdy box
Calibration	S6
Type of product	3-point bore gauge

Services

Calibration Internal micrometer set Measuring range 6-10 mm	020550 6-10
---	-------------

Accessories

Connection cable Duplex Type USB2	498951 USB2
Setting ring DIN 2250 C Nominal size Ø 9 mm	484030 9
Connection cable Duplex Type R2	498951 R2
Button cell / special battery Battery type CR2032	081560 CR2032
Extension for internal micrometers Type 1/63	428510 1/63
Setting ring DIN 2250 C Nominal size Ø 7 mm	484030 7