

Garant**Cutting disc, stainless steel EXTRA THIN, Disc Ø / quantity: 125/500**

Order data

Order number	GG5272 125/500
GTIN	4067263136972
Item class	GGN

Description

Version:

Special type for **stainless steel**.

New **high-performance version** using state of the art technology with significant productivity advantages and excellent cutting qualities. **Increased cutting performance** due to rough free-grinding side faces; **improved service life**.

The thinness of the disc allows **very quick** cutting **with low force and optimum time saving**.

Clean cut edges, virtually no burrs. Corresponds to No. 563272.

Specification:

A60R-BF.

Technical description

Contents	500
Specification	A60R-BF
Shape description	straight
Bore Ø	22.23 mm
Disc Ø	125 mm
Disc thickness	1 mm

for material thicknesses	3 - 5 mm
Grinding medium code	A
Iron, sulphur and chlorine constituents	< 0.1 %
recommended approach angle	Radius degrees
optimised for material	INOX
Propulsive equipment	Angle grinder
maximum circumferential speed	80 m/s
Type of product	Cutting disc

User data

	Suitability	V _c	ISO code
Alu Mg	suitable only under restricted conditions		
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable		
INOX	suitable		
Ti	suitable		
GG(G)	suitable only under restricted conditions		
CuZn	suitable only under restricted conditions		
Plastic, GRP	suitable only under restricted conditions		
Uni	suitable only under restricted conditions		
dry	suitable		

Accessories

Cutting disc, high-performance versionEXTRA THIN,
STAINLESS STEEL Disc Ø 125 mm

563272 125