



Digital XTL bore gauge with Bluetooth, Measurement range: 50-65mm



Order data

Order number	428761 50-65
GTIN	2050002078055
Item class	46B

Description

Version:

3-point bore gauges for blind hole measurement from size 12.5–16. Fixed carbide measuring jaws, from size 12.5–16 with carbide inserts. Large, sharp contrast digital display. Reliable measurement without a vernier. Excellently suitable for measuring vertical holes.

Function:

- **mm / inch selection.**
- **Setting 2 preset values.**
- **On / Off data storage button.**

Supplied with:

Measuring lever, micrometer head with UKAS test certificate, 1 battery No. 081560 size CR2032.

Optional extras:

Data cable No. 498950 (from size 20), No. 498951 (up to size 20), setting rings No. 484030, extensions No. 428510.

Technical description

Article no of the battery / rechargeable battery fitted	081560 CR2032
Error limit	0.005 mm

Data sheet

Standard measuring depth	80 mm
Dimension a	0.5 mm
Measuring depth with extension	230 mm
Scale divisions	0.001 mm
Number of batteries contained	1
Measuring range	50 - 65 mm
Power supply	Battery-powered
Standard	DIN 863
Reversible reading	mm / inch
Interface	RS232C interface
Interface	USB interface
Interface	Bluetooth interface
Measurement technology	digital
Packaging	sturdy box
Calibration	B6
Type of product	3-point bore gauge

Services

Calibration 3-point internal micrometer maximum measuring range 100 mm	022500 100
DAkkS calibration 3-point internal micrometer maximum measuring range 200 mm	022510 200

Accessories

Multi-receiver / USB keyboard interface Type	498975
Extension for internal micrometers Type 5/150	428510 5/150
Setting ring DIN 2250 C Nominal size Ø 60 mm	484030 60
Setting ring DIN 2250 C Nominal size Ø 55 mm	484030 55
Setting ring DIN 2250 C Nominal size Ø 65 mm	484030 65

Connection cable Duplex Type 2	498950 2
Connection cable Duplex Type USB2	498950 USB2
Setting ringDIN 2250 C Nominal size Ø 50 mm	484030 50
Receiver / USB keyboard interface Type	498965
Button cell / special battery Battery type CR2032	081560 CR2032
Setting ringDIN 2250 C Nominal size Ø 61 mm	484030 61
Setting ringDIN 2250 C Nominal size Ø 63 mm	484030 63
Setting ringDIN 2250 C Nominal size Ø 52 mm	484030 52
Setting ringDIN 2250 C Nominal size Ø 62 mm	484030 62
Setting ringDIN 2250 C Nominal size Ø 56 mm	484030 56
Setting ringDIN 2250 C Nominal size Ø 54 mm	484030 54
Setting ringDIN 2250 C Nominal size Ø 53 mm	484030 53
Setting ringDIN 2250 C Nominal size Ø 64 mm	484030 64
Setting ringDIN 2250 C Nominal size Ø 51 mm	484030 51
Setting ringDIN 2250 C Nominal size Ø 57 mm	484030 57
Setting ringDIN 2250 C Nominal size Ø 59 mm	484030 59
Setting ringDIN 2250 C Nominal size Ø 58 mm	484030 58