



Digital XTL internal quick measuring set with Bluetooth, Measurement range: 10-20mm



Order data

Order number	428771 10-20
GTIN	2050002078109
Item class	46B

Description

Version:

3-point XT internal micrometer series for blind hole measurement from size 12.5–16. Fixed carbide measuring jaws, from size 12.5–16 with carbide inserts. Large, sharp contrast digital display. Reliable measurement without a vernier. Excellently suitable for measuring vertical holes.

Function:

- **mm / inch selection.**
- **Setting 2 preset values.**
- **On / Off data storage button.**

Supplied with:

Digital internal micrometers No. 428760 and setting rings with UKAS test certificate.

Technical description

Scale divisions	0.001 mm
Error limit	0.004 mm
Article no of the battery / rechargeable battery fitted	081560 CR2032

Data sheet

Number of measuring heads	3
Setting ring Ø	12.5 / 20 mm
Measuring range	10 - 20 mm
Power supply	Battery-powered
Number of batteries contained	1
Standard	DIN 863
Reversible reading	mm / inch
Interface	RS232C interface
Interface	USB interface
Interface	Bluetooth interface
Measurement technology	digital
Packaging	sturdy box
Calibration	S6
Type of product	3-point bore gauge

Services

Calibration Internal micrometer set Measuring range 10-20 mm	020550 10-20
--	--------------

Accessories

Setting ring DIN 2250 C Nominal size Ø 14 mm	484030 14
Button cell / special battery Battery type CR2032	081560 CR2032
Setting ring DIN 2250 C Nominal size Ø 11 mm	484030 11
Extension for internal micrometers Type 2/76	428510 2/76
Connection cable Duplex Type USB2	498951 USB2
Extension for internal micrometers Type 3/100	428510 3/100
Connection cable Duplex Type R2	498951 R2
Setting ring DIN 2250 C Nominal size Ø 18 mm	484030 18