

Garant**Thread cutting set with tap sets, 3 pieces, for metric threads: M3-12****Order data**

Order number	145114 M3-12
GTIN	4067263125006
Item class	11K

Description**Version:**

Strong sheet metal case with carrying handle and 2 offset catches. Each tool is securely stored and protected in a foam insert and is immediately ready to hand. The taps are raised up vertically when the lid is opened. For more detailed descriptions of the content see individual products.

Content:

- 1 each tap set, 3 pieces, No. 130150: Size M3; M4; M5; M6; M8; M10; M12
- 1 each die No. 140300: Size M3; M4; M5; M6; M8; M10; M12
- 1 each jobber drill No. 114150: Size 2.5; 3.3; 4.2; 5; 6.8; 8.5; 10.2
- 1 each adjustable tap wrench No. 148410: Size 1; 2
- 1 toolholder with ratchet No. 148701: Size 85
- 1 each die stock No. 149310: Size 20×5; 20×7; 25×9; 30×11; 38×14
- 1 thread gauge No. 477000: Size M/W
- 1 screwdriver No. 664300: Size 3×60

Technical description

Length	418 mm
for metric threads	M3 – M12
Height	58 mm

Width	229 mm
Thread type	M
Flank angle	60 degrees
Type of product	Die

Accessories

HSS jobber drillN Ø DC h8 (mm or inch) 10,2	114150 10,2
HSS jobber drillN Ø DC h8 (mm or inch) 2,5	114150 2,5
HSS jobber drillN Ø DC h8 (mm or inch) 3,3	114150 3,3
HSS jobber drillN Ø DC h8 (mm or inch) 4,2	114150 4,2
HSS jobber drillN Ø DC h8 (mm or inch) 5	114150 5
HSS jobber drillN Ø DC h8 (mm or inch) 6,8	114150 6,8
HSS jobber drillN Ø DC h8 (mm or inch) 8,5	114150 8,5
Hand tap set M M10	130150 M10
Hand tap set M M12	130150 M12
Hand tap set M M3	130150 M3
Hand tap set M M4	130150 M4
Hand tap set M M5	130150 M5
Hand tap set M M6	130150 M6
Hand tap set M M8	130150 M8
Die6g M M10	140300 M10
Die6g M M12	140300 M12
Die6g M M3	140300 M3
Die6g M M4	140300 M4
Die6g M M5	140300 M5
Die6g M M6	140300 M6
Die6g M M8	140300 M8
	145605 M3-12

Sheet metal case empty for thread cutting set for metric threads M3-12

Tap wrench, adjustable Type 1	148410 1
Tap wrench, adjustable Type 2	148410 2
T-tap wrench with ratchet Overall length 85 mm	148700 85
Die stock for die $\varnothing \times$ height 20X5 mm	149310 20X5
Die stock for die $\varnothing \times$ height 20X7 mm	149310 20X7
Die stock for die $\varnothing \times$ height 25X9 mm	149310 25X9
Die stock for die $\varnothing \times$ height 30X11 mm	149310 30X11
Die stock for die $\varnothing \times$ height 38X14 mm	149310 38X14
Thread gauge for threads M/W	477000 M/W