

**Garant****Thread cutting set with spiral point taps, for metric threads: M3-12****Order data**

Order number	145314 M3-12
GTIN	4067263118367
Item class	11K

**Description****Version:**

**Strong sheet metal case** with carrying handle and 2 offset catches. Each tool is securely stored and protected in a foam insert and is immediately ready to hand. The taps are raised up vertically when the lid is opened. For more detailed descriptions of the content see individual products.

**Content:**

3 each spiral point taps No. 131450: Size M3; M4; M5; M6; M8; M10; M12

1 each die No. 140300: Size M3; M4; M5; M6; M8; M10; M12

1 each jobber drill No. 114150: Size 2.5; 3.3; 4.2; 5; 6.8; 8.5; 10.2

1 each adjustable tap wrench No. 148410: Size 1; 2

1 toolholder with ratchet No. 148701: Size 85

1 each die stock No. 149310: Size 20x5; 20x7; 25x9; 30x11; 38x14

1 thread gauge No. 477000: Size M/W

1 screwdriver No. 664300: Size 3x60

**Technical description**

Width	223 mm
Height	55 mm
Length	420 mm

for metric threads	M3 – 12
Thread type	M
Flank angle	60 degrees
Type of product	Die

## Accessories

HSS jobber drillIN Ø DC h8 (mm or inch) 10,2	114150 10,2
HSS jobber drillIN Ø DC h8 (mm or inch) 2,5	114150 2,5
HSS jobber drillIN Ø DC h8 (mm or inch) 3,3	114150 3,3
HSS jobber drillIN Ø DC h8 (mm or inch) 4,2	114150 4,2
HSS jobber drillIN Ø DC h8 (mm or inch) 5	114150 5
HSS jobber drillIN Ø DC h8 (mm or inch) 6,8	114150 6,8
HSS jobber drillIN Ø DC h8 (mm or inch) 8,5	114150 8,5
Spiral point tapshort M M10	131450 M10
Spiral point tapshort M M12	131450 M12
Spiral point tapshort M M3	131450 M3
Spiral point tapshort M M4	131450 M4
Spiral point tapshort M M5	131450 M5
Spiral point tapshort M M6	131450 M6
Spiral point tapshort M M8	131450 M8
Die6g M M10	140300 M10
Die6g M M12	140300 M12
Die6g M M3	140300 M3
Die6g M M4	140300 M4
Die6g M M5	140300 M5
Die6g M M6	140300 M6
Die6g M M8	140300 M8
	145605 M3-12

Sheet metal case empty for thread cutting set for metric threads M3-12

Tap wrench, adjustable Type 1	148410 1
Tap wrench, adjustable Type 2	148410 2
T-tap wrench with ratchet Overall length 85 mm	148700 85
Die stock for die $\varnothing \times$ height 20X5 mm	149310 20X5
Die stock for die $\varnothing \times$ height 20X7 mm	149310 20X7
Die stock for die $\varnothing \times$ height 25X9 mm	149310 25X9
Die stock for die $\varnothing \times$ height 30X11 mm	149310 30X11
Die stock for die $\varnothing \times$ height 38X14 mm	149310 38X14
Thread gauge for threads M/W	477000 M/W